

Alfa Romeo

	Luz Baja	Luz Alta	Antiniebla	DelanteraPosición	DelanteraIntermit	LateralGiro	TraseraIntermiten	TraserasPosición	Freno	TraseraAntiniebla	Marcha Atrás	Patente
Alfa 33 >12/90	H4	H4		T4W	P21W		P21W	R5W	P21/5W	P21W	P21W	R5W
	I2342	I2342		I2929	I2498		I2498	I282I	I2499	I2498	I2498	I282I
Alfa 33 >12/95	H4	H4	H3	W5W	P21W		P21W	R5W	P21W	P21W	P21W	R5W
	I2342	I2342	I2336	I296I	I2498		I2498	I282I	I2498	I2498	I2498	I282I
Alfa 33 Sportwagen	H4	H4	H3	W5W	P21W		P21W	R5W	P21W	P21W	P21W	R5W
90-95	I2342	I2342	I2336	I296I	I2498		I2498	I282I	I2498	I2498	I2498	I282I
Alfa 75 85-93	H4	H4	H3	T4W	P21W		P21W	R5W	P21W	P21W	P21W	CSW
	I2342	I2342	I2336	I2929	I2498		I2498	I282I	I2498	I2498	I2498	I2844
Alfa 90 85-87	H4	H4	H2	W5W	P21W		P21W	R5W	P21W	P21W	P21W	R5W
	I2342	I2342	I231I	I296I	I2498		I2498	I282I	I2498	I2498	I2498	I282I
Alfa 145/146 94>	H4	H4		W5W	P21W	W5W	P21/5W	P21/5W	P21/5W	P21W	P21W	W5W
	I2342	I2342		I296I	I2498	I296I	I2499	I2499	I2499	I2498	I2498	I296I
Alfa 145/146 96>	H1	H1	H1	W5W	PY21W		P21W	P21/5W	P21/5W	P21W	P21W	W5W
	I2258	I2258	I2258	I296I	I2496		I2498	I2499	I2499	I2498	I2498	I296I
Alfa 147 >00	H7	H7	H1	W5W	PY21W		P21W	P21/5W	P21/5W	P21W	P21W	W5W
	I2972	I2972	I2258	I296I	I2496		I2498	I2499	I2499	I2498	I2498	I296I
Alfa 155 92>	H1	H1	H1	W5W	P21W		P21W	R5W	P21/5W	P21W	P21W	W5W
	I2258	I2258	I2258	I296I	I2498		I2498	I282I	I2499	I2498	I2498	I296I
Alfa 156 96>	H7	H1	H1	TW4	PY21W	W5W	PY21W	P21/5W	P21/5W	P21W	P21W	W5W
	I2972	I2258	I2258	I2929	I2496	I296I	I2496	I2499	I2499	I2498	I2498	I296I
Alfa 156 sportwagon	H7	H1	H1	TW4	PY21W	W5W	PY21W	P21/5W	P21/5W	P21W	P21W	W5W
>00	I2972	I2258	I2258	I2929	I2496	I296I	I2496	I2499	I2499	I2498	I2498	I296I
Alfa 164 87>	H4	H4	H3	W5W	P21W	W5W	P21W	R10W	P21W	P21W	P21W	W5W
	I2342	I2342	I2336	I296I	I2498	I296I	I2498	I2814	I2498	I2498	I2498	I296I
Alfa 166 >00	H7/D2S	HB3	H3	W5W	P21W	W5W	P21W	R5W	P21W	P21W	P21W	W5W
	I2972/85122	9005	I2336	I296I	I2498	I296I	I2498	I282I	I2498	I2498	I2498	I296I
Alfasud 73-88	H4	H4		TW4	P21W	W5W	P21W	R5W	P21W	P21W	P21W	R5W
	I2342	I2342		I2929	I2498	I296I	I2498	I282I	I2498	I2498	I2498	I282I
Alfasud Sprint/TI	H1	H1		W5W	P21W		P21W	R5W	P21W		P21W	R5W
78-89	I2258	I2258		I296I	I2498		I2498	I282I	I2498		I2498	I282I
GTV 2L/GTV6 2,5L	H1	H1		W5W	P21W		P21W	R5W	P21W	P21W	P21W	R5W
81-88	I2258	I2258		I296I	I2498		I2498	I282I	I2498	I2498	I2498	I282I
Alfetta Quadrifoglio	H1	H1		TW4	P21W		P21W	R5W	P21W	P21W	P21W	TW4
83-86	I2258	I2258		I2929	I2498		I2498	I282I	I2498	I2498	I2498	I2929
Arna 83-86	H4	H4		TW4	P21W		P21W	R5W	P21W	P21W	P21W	R5W
	I2342	I2342		I2929	I2498		I2498	I282I	I2498	I2498	I2498	I282I
Guilietta 79-86	H4	H4		TW4	P21W		P21W	R5W	P21W	P21W	P21W	TW4
	I2342	I2342		I2929	I2498		I2498	I282I	I2498	I2498	I2498	I2929
GTV 6TB	HB3	HB3		W5W	P21W	W5W	P21W	R5W	P21W	P21W	P21W	W5W
	9005	9005		I296I	I2498	I296I	I2498	I282I	I2498	I2498	I2498	I296I
Spider	HB3	HB3		W5W	P21W		P21W	T4W	P21W	P21W	P21W	W5W
	9005	9005		I296I	I2498		I2498	I2929	I2498	I2498	I2498	I296I